

WATO EX - 35

Anesthesia Machine

Touch From Now

- Easy Setting by Touch
- Touchable Smart Alarm Management




Better Performance

- Innovation P-n-P Gas Monitoring
- Driven Gas Auto-switch



High Performance Ventilator

- Volume Controlled Ventilation (VCV)
- Pressure Controlled Ventilation (PCV)
- Pressure Controlled Ventilation + Apnea Ventilation (PSV + Apnea Ventilation)
- Synchronized Intermittent Mandatory Ventilation – VS (SIMV-VC)
- Synchronized Intermittent Mandatory Ventilation – PC (SIMV-PC)



- 3 Gas system available (O2, AIR and N2O)
- Classical gas tube flowmeters
- Ventilator with pneumatic driven and electronic control
- Large CO2 Absorber (sodalime) 1,5 Litre with quick release canister
- Ventilator Mode : Spontaneous/Manual/VCV/PVC
- Auxiliary Common Gas Outlet (ACGO) For Extended
- Ergonomic working environment with LED light stripe
- 2 Position vaporizer for halothane, isoflurane, sevoflurane, enflurane or desflurane agent
- Standar Auxiliary power outlets